

Significance of Use

Hexavalent chromium salts are used in various industrial applications, such as in the manufacture of paints, dyes, explosives, and ceramics, and extensively in the metal finishing and plating industries. Due to its toxicity to humans, animals, and aquatic life, hexavalent chromium is actively monitored and neutralized in wastewater from the above industries.

| Specifications | HI96723 | | HI96749 |
|---------------------------|--|----------------------|------------------------|
| | Chromium VI HR | | Chromium VI LR |
| Range | 0 to 1000 μg/L (ppb) | | 0 to 300 μg/L (ppb) |
| Resolution | 1 μg/L | | 1 μg/L |
| Accuracy @ 25°C (77°F) | ±5 μg/L ±4% of read | ling | ±1 μg/L ±4% of reading |
| Light Source | tungsten lamp | | |
| Light Detector | silicon photocell with narrow band interference filter @ 525 nm | | |
| Power Supply | 9V battery | | |
| Auto-off | after ten minutes of non-use in measurement mode; after one hour of non-use in calibration mode; with last reading reminder | | |
| Environment | 0 to 50°C (32 to 122°F); RH max 95% non-condensing | | |
| Dimensions | 193 x 104 x 69 mm (7.6 x 4.1 x 2.7") | | |
| Weight | 360 g (12.7 oz.) | | |
| Method | adaptation of the ASTM Manual of Water and Environmental Technology, D1687-92, diphenylcarbohyzide method. | | |
| Ordering Information | HI96723 and HI96749 are supplied with sample cuvettes (2) with caps, 9V battery, instrument quality certificate and instruction manual. CAL Check™ standards and testing reagents sold separately | | |
| Reagents and Standards | HI96723-11 | CAL Check™ standar | d cuvettes |
| | HI96749-11 | CAL Check™ standar | d cuvettes |
| | HI93723-01 | reagents for 100 tes | ts |
| | HI93723-03 | reagents for 300 tes | its |
| | HI93749-01 | reagents for 100 tes | ts |
| | HI93749-03 | reagents for 300 tes | its |

HI96723 · HI96749

Chromium VI HR and LR Portable Photometers

CAL Check

 Allows for performance verification and calibration of the meter using NIST traceable standards.

• GLP

Review of the last calibration date.

Auto-shut off

 Automatic shut off after 10 minutes of non-use when the meter is in measurement mode. Prevents wastage of batteries in the event the meter is accidentally left on.

• Battery status indicator

 Indicates the amount of battery life left.

• Built-in timer

 Display of time remaining before a measurement is taken. Ensures that all readings are taken at the appropriate reaction intervals for the test being performed.

Error messages

 Messages on display alerting to problems including no cap, high zero, and standard too low.

• Cooling lamp indicator

To maintain the desirable wavelength to be used for absorbance, it is necessary to ensure components are not overheated from the heat generated by the tungsten lamp. Each photometer is designed to allow a minimal amount of time for components to cool. The cooling lamp indicator is displayed prior to a reading being taken.

• Units of measure

 Appropriate unit of measure is displayed along with reading.

The HI96723 and HI96749 portable photometers are for the measurement of chromium VI. Hanna's portable photometers feature an advanced optical system; the combination of a special tungsten lamp, a narrow band interference filter, and silicon photodetector ensure accurate photometric readings every time. The Hanna exclusive CAL Check™ feature utilizes ready-made, NIST traceable standards to verify both meter validation and calibration. The exclusive cuvette locking system ensures that the cuvette is inserted into the measurement cell in the same position every time to maintain a consistent path length.

